

**Garant**

**Bevel edge square, flat version stainless, accuracy class 00, Stock length: 150X100mm**

**Order data**

Order number	450010 150X100
GTIN	4045197443960
Item class	41G

**Description****Version:**

**Very high accuracy.** With two bevelled straight edges on the long blade.  
Through hardened and stress-relieved. Test faces ground and lapped, other faces ground.

**Application:**

For inspection work using the light gap principle.

**Technical description**

Shank cross-section	30x6 mm
Length of short arm	100 mm
Right angle tolerance	0.004 mm
Length of long arm	150 mm
Standard	DIN 875/00
Material	Stainless steel, INOX

all parts	hardened
Packaging	sturdy box
Calibration	F1
Type of product	Bevel square

## Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750