

**Garant****Try square stainless, accuracy class 0, Stock length: 150X100mm****Order data**

Order number	451020 150X100
GTIN	4045197443861
Item class	41G

**Description****Version:**

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

**Application:**

For inspection and high precision work.

**Accuracy:**

**DIN 875 / 0** – angle tolerance e.g. for size 100×70 = 0.007 mm.

**Technical description**

Right angle tolerance	0.008 mm
Shank cross-section	30×6 mm
Stock length	150×100 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

### Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750

### Accessories

Wooden case for stock length 150X100 mm	451600 150X100
---	----------------