

Mitutoyo
External micrometer with Vee-anvil, Measuring range: 10-25mm

Order data

Order number	422300 10-25
GTIN	4946368009971
Item class	44A

Description
Version:

With Vee anvil for measuring three or five-flute cutters. Enamelled frame. Spindle pitch correction for Vee angle. **Triangular** with a Vee angle of 60°.

Application:

For measuring **3 or 5 flute cutters** (end mills, reamers).

Supplied with:

Setting standard.

Technical description

Measuring range	10 - 25 mm
Spindle Ø	6.35 mm
Barrel Ø	18 mm
Vee angle	60 (triangular) degrees
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Calibration	B8
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box

Type of product

External micrometer

Services

Calibration Thread flanks external micrometer including setting dimension maximum nominal size 100 mm

022320 100