

**External blade micrometer, Measuring range: 25-50mm****Order data**

Order number	422410 25-50
GTIN	4059192003791
Item class	43A

Description**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Micrometer barrel graduations	1/50 mm
Flat blade anvils width	0.75 mm
Measuring range	25 - 50 mm
Spindle pitch	0.5 mm
Flat blade anvils length	6.5 mm
Spindle Ø	8 mm
Scale divisions	0.01 mm
Calibration	B1
Calibration	B2
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/422410-25-50>