



Thread measurement wires set, Wire \varnothing : 0,250mm



Order data

Order number	422490 0,250
GTIN	2050001063496
Item class	46P

Description

Version:

The thread measurement wires are hardened and precision lapped, the holders are matt chrome-plated. A snap ring in the mounting bore ensures secure easy-twist seating on the measuring spindle.

Application:

For determining the flank \varnothing of external threads using the three-wire method in conjunction with an external micrometer or a length measurement bench.

Supplied with:

A set consists of a holder with one measurement wire and a holder with two measurement wires, in a plastic box.

Note:

When ordering, please specify the \varnothing of the measuring spindle (6.35 mm / 6.5 mm / 6.8 mm / 7.5 mm / 8.0 mm).

Technical description

for thread pitch P	0.4
Wire \varnothing	0.25 mm
for threads	M2 / M2.3
Check gauge M to DIN 13 sheet 1	2.145 / 2.444 mm

Error limit	±1 µm
Packaging	sturdy box
Calibration	L16
Type of product	Thread measurement wire
for spindle Ø	6.35 mm
for spindle Ø	6.5 mm
for spindle Ø	6.8 mm
for spindle Ø	7.5 mm
for spindle Ø	8 mm

Services

Calibration Thread measurement wire Type GMD	028900 GMD
DAkkS calibration Thread measurement wire Type GMD	028910 GMD