

**Garant****Try square stainless, accuracy class 0, Stock length: 200X130mm**

## Order data

Order number	451020 200X130
GTIN	4045197443878
Item class	41G

## Description

**Version:**

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

**Application:**

For inspection and high precision work.

**Accuracy:**

**DIN 875 / 0** – angle tolerance e.g. for size 100×70 = 0.007 mm.

## Technical description

Shank cross-section	30×7 mm
Right angle tolerance	0.009 mm
Stock length	200×130 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

### Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750

### Accessories

Wooden case for stock length 200X130 mm	451600 200X130
---	----------------