

Garant**Stock square stainless, accuracy class 1, Stock length: 75X50mm****Order data**

Order number	451030 75X50
GTIN	4045197443885
Item class	41G

Description**Version:**

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Supplied in a plastic box.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Technical description

Shank cross-section	15×4 mm
Right angle tolerance	0.014 mm
Stock length	75×50 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100

Accessories

Wooden case for stock length 75X50 mm	451600 75X50
---------------------------------------	--------------