

Mitutoyo
Digital external micrometer for groove measurement, Measuring range: 0-25mm

Order data

Order number	421640 0-25
GTIN	4946368689852
Item class	44A

Description
Version:

Clear (7.5 mm high), digital measured value display provides quick readings. Addition reading by vernier. Sintered, precision lapped, carbide tipped anvils, measuring spindle hardened and ground. Locking by clamping screw. Measuring force at the ratchet 5 - 10 N.

Supplied with:

From size 25-50 including 1 setting standard. 1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445.

Technical description

Measuring range	0 - 25 mm
Calibration	B1
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital

Packaging	sturdy box
Type of product	External micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25

Accessories

Multi-receiver / USB keyboard interface Type	498975
Connecting cable with data switch Type D2	497445 D2
Connecting cable with data switch Type USB2	497445 USB2
Transmitter Type S16E	498966 S16E
Connecting cable with data switch Type D1	497445 D1
Button cell / special battery Battery type 357	081560 357
Receiver / USB keyboard interface Type	498965