

**Stock square Accuracy class 2, Stock length: 300X175mm****Order data**

Order number	452590 300X175
GTIN	4045197372161
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Right angle tolerance	0.05 mm
Shank cross-section	35×7 mm
Stock length	300×175 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

Services

Calibration Stock, try, and bevel edge squares maximum arm length 300 mm

025000 300

DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm

025010 750