

Mitutoyo

Digital external micrometer with data output, Measuring range: 0-25mm



Order data

Order number	421572 0-25
GTIN	4946368716602
Item class	44A

Description

Version:

Error limits more accurate than the requirements of **DIN 863**. Extra large LCD display (7.5 mm). "Function Lock" prevents accidental readjustment of the zero point. **Combination ratchet** (torque limitation in the barrel and in the quick drive) for one-handed use and use in a holder.

Advantage:

Measuring time reduction of up to 40% due to 2 mm spindle pitch.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357. From size 25-50, 1 setting standard.

Optional extras:

Data cable No. 497445.

Technical description

Spindle Ø	6.35 mm
Spindle pitch	2 mm
Measuring range	0 - 25 mm
Error limit	2 µm
Scale divisions	0.001 mm
Calibration	B1

Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	USB interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

Accessories

Connecting cable with data switch Type D1	497445 D1
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type USB2	497445 USB2
Button cell / special battery Battery type 357	081560 357
Transmitter Type S16E	498966 S16E
Multi-receiver / USB keyboard interface Type	498975
Connecting cable with data switch Type D2	497445 D2