

Garant**Stock square stainless, accuracy class 0, Stock length: 75X50mm****Order data**

Order number	451010 75X50
GTIN	4045197444066
Item class	41G

Description**Version:**

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 0 – angle tolerance e.g. for size 100×70 = 0.007 mm.

Technical description

Shank cross-section	15×4 mm
Right angle tolerance	0.007 mm
Stock length	75×50 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

Services

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750

Accessories

Wooden case for stock length 75X50 mm	451600 75X50
---------------------------------------	--------------