

**Garant****Stock square stainless, accuracy class 1, Stock length: 100X70mm****Order data**

Order number	451030 100X70
GTIN	4045197443892
Item class	41G

**Description****Version:**

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Supplied in a plastic box.

**Application:**

For inspection and high precision work.

**Accuracy:**

**DIN 875 / 1** – angle tolerance e.g. for size 100×70 = 0.015 mm.

**Technical description**

Right angle tolerance	0.015 mm
Shank cross-section	20×5 mm
Stock length	100×70 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

### Services

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750

### Accessories

Wooden case for stock length 100X70 mm	451600 100X70
--	---------------