

**Mitutoyo**
**Digital external micrometer for groove measurement, Measuring range: 25-50mm**

**Order data**

Order number	421640 25-50
GTIN	4946368508009
Item class	44A

**Description**
**Version:**

**Clear (7.5 mm high), digital measured value display provides quick readings. Addition reading by vernier.** Sintered, precision lapped, carbide tipped anvils, measuring spindle hardened and ground. Locking by clamping screw. Measuring force at the ratchet 5 - 10 N.

**Supplied with:**

From size 25-50 including 1 setting standard. 1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445.

**Technical description**

Measuring range	25 - 50 mm
Calibration	B2
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital

Packaging	sturdy box
Type of product	External micrometer

## Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

## Accessories

Connecting cable with data switch Type D2	497445 D2
Connecting cable with data switch Type USB2	497445 USB2
Transmitter Type S16E	498966 S16E
Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type D1	497445 D1
Micrometer setting standard overall length 25 mm	421100 25
Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965