

Garant**Stock square stainless, accuracy class 0, Stock length: 100X70mm**

Order data

Order number	451010 100X70
GTIN	4045197444073
Item class	41G

Description

Version:

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 0 – angle tolerance e.g. for size 100×70 = 0.007 mm.

Technical description

Shank cross-section	20×5 mm
Right angle tolerance	0.007 mm
Stock length	100×70 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/451010-100X70>