

**Stock square Accuracy class 2, Stock length: 500X250mm****Order data**

Order number	452590 500X250
GTIN	4045197372185
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Right angle tolerance	0.07 mm
Shank cross-section	40×8 mm
Stock length	500×250 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

Services

Calibration Stock, try, and bevel edge squares maximum arm length 750 mm

025000 750

DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm

025010 750