

Garant**Stock square stainless, accuracy class 1, Stock length: 150X100mm****Order data**

Order number	451030 150X100
GTIN	4045197444103
Item class	41G

Description**Version:**

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Supplied in a plastic box.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Technical description

Shank cross-section	30×6 mm
Right angle tolerance	0.018 mm
Stock length	150×100 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300

Accessories

Wooden case for stock length 150X100 mm	451600 150X100
---	----------------