

Garant**Try square stainless, accuracy class 1, Stock length: 250X165mm****Order data**

Order number	451040 250X165
GTIN	4045197444219
Item class	41G

Description**Version:**

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Protective packaging for safe transport.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Technical description

Shank cross-section	35×7 mm
Right angle tolerance	0.023 mm
Stock length	250×165 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750

Accessories

Wooden case for stock length 250X165 mm	451600 250X165
---	----------------