

**Mitutoyo****Digital external micrometer for thread measurements, Measuring range: 0-25mm****Order data**

Order number	421650 0-25
GTIN	4946368695761
Item class	44A

**Description****Version:**

**Clear (7.5 mm high), digital measured value display provides quick readings. Addition reading by vernier.** Sintered, precision lapped, carbide tipped anvils, measuring spindle hardened and ground. Locking by clamping screw. Measuring force at the ratchet 5 - 10 N.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

From size 25-50 including 1 setting standard. 1 battery No. 081560 size 357.

**Without setting standards.****Optional extras:**

Data cable No. 497445.

Anvils for thread measurement No. 421652.

**Technical description**

Measuring range	0 - 25 mm
Calibration	B1
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered

Pitch error	3 µm
Standard	ISO 3611
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Type of product	External micrometer

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/421650-0-25>