

**Stock square Accuracy class 2, Stock length: 75X50mm****Order data**

Order number	452590 75X50
GTIN	4045197372116
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Shank cross-section	15×5 mm
Right angle tolerance	0.028 mm
Stock length	75×50 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

Services

Calibration Stock, try, and bevel edge squares maximum arm length 100 mm

025000 100

DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm

025010 750

Accessories

Wooden case for stock length 75X50 mm

451600 75X50