

**External blade micrometer, Measuring range: 0-25mm****Order data**

Order number	421900 0-25
GTIN	4045197203953
Item class	42B

Description**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Spindle Ø	8 mm
Micrometer barrel graduations	1/50 mm
Measuring range	0 - 25 mm
Flat blade anvils length	6.5 mm
Spindle pitch	0.5 mm
Flat blade anvils width	0.75 mm
Scale divisions	0.01 mm
Calibration	B1
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box

Type of product

External micrometer

ServicesCalibration External micrometer without setting dimension
maximum measuring range 25 mm

022000 25

DAkkS calibration External micrometer without setting
dimension maximum measuring range 100 mm

022010 100