

**Try square Accuracy class 2, Stock length: 75X50mm****Order data**

Order number	452600 75X50
GTIN	4045197205766
Item class	42F

**Description****Version:**

All faces and edges ground. Inspection test faces ground.

**Application:**

For accurate general workshop work.

**Accuracy:**

**DIN 875 / 2** – angle tolerance e.g. for size 100×70 = 0.030 mm.

**Technical description**

Shank cross-section	15×5 mm
Right angle tolerance	0.028 mm
Stock length	75×50 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Try squares

**Services**DAkkS calibration  
Stock, try, and bevel edge squares  
maximum arm length 750 mm

025010 750

Calibration  
Stock, try, and bevel edge squares maximum  
arm length 100 mm

025000 100

**Accessories**

Wooden case for stock length 75X50 mm

451600 75X50