

Garant**Try square stainless, accuracy class 1, Stock length: 400X265mm**

Order data

Order number	451040 400X265
GTIN	4045197444233
Item class	41G

Description

Version:

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Protective packaging for safe transport.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Packaging: sturdy box

Calibration: F1

Right angle tolerance: 0.03 mm

Shank cross-section: 45×10 mm

Technical description

Right angle tolerance	0.03 mm
Shank cross-section	45×10 mm
Stock length	400×265 mm

Calibration	F1
Standard	DIN 875
Accuracy	1
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

Services

Calibration Stock, try, and bevel edge squares maximum arm length 750 mm	015020 750
Labelling laser-etched Type	018940
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	015600 750
Recalibration Stock, try, and bevel edge squares maximum arm length 750 mm	025000 750
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	025010 750

Accessories

Wooden case for stock length 400X265 mm	451600 400X265
---	----------------