



External thread micrometer without anvils, Measuring range: 75-100mm



Order data

Order number	422340 75-100
GTIN	4250099618389
Item class	46P

Description

Version:

Hardened and ground measuring spindle with bore for the measuring tips. Glare-free satin chrome-plated barrel. With sensitive ratchet (friction lock) and quick drive for rapid adjustment. Heat-insulated frame.

Application:

For practical measurement of flank \varnothing of external threads. One pair of anvils (Vee and cone) fits several pitches, providing the flank angle remains unchanged.

Supplied with:

From size 25–50 with $1 \times 60^\circ$ setting standard; without thread measurement inserts.

Optional extras:

Vee and cone anvils No. 421652.

Note:

Further measurement ranges available on request.

Technical description

Spindle \varnothing	6.5 mm
Spindle pitch	0.5 mm
Micrometer barrel graduations	1/50 mm
Barrel \varnothing	20 mm
Measuring range	75 - 100 mm
Scale divisions	0.01 mm

Calibration	Price on request
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Accessories

Pair of anvils for external thread micrometers Pitch 0,6-0,9 mm	421652 0,6-0,9
Pair of anvils for external thread micrometers Pitch 1-1,75 mm	421652 1-1,75
Pair of anvils for external thread micrometers Pitch 0,4-0,5 mm	421652 0,4-0,5
Pair of anvils for external thread micrometers Pitch 3,5-5 mm	421652 3,5-5
Pair of anvils for external thread micrometers Pitch 5,5-7 mm	421652 5,5-7
Pair of anvils for external thread micrometers Pitch 2-3 mm	421652 2-3