

**Stock square Accuracy class 2, Stock length: 750X375mm****Order data**

Order number	452590 750X375
GTIN	4045197372307
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Shank cross-section	45×10 mm
Right angle tolerance	0.095 mm
Stock length	750×375 mm
Standard	DIN 875
Accuracy	2
Type of product	Stock square

