




## Stepped tenon ground, Slot size b<sub>1</sub> of the machine: 12mm



### Order data

Order number	375365 12
GTIN	4020772071561
Item class	35A

### Description

#### Version:

Precision ground all round, resulting in quick alignment times for appliances, vices etc., which are to be aligned parallel to the table slots of machine tools. A dial indicator is thus no longer required.

#### Application:

**These tenons are screwed in pairs into the standard 20mm-wide tenon slot of jigs.** By changing the tenons it is possible to work **on several machines with different slot widths** with one jig each.

#### Material:

Steel C 15, case-hardened.

#### Accuracy:

**Dimension b = fit h6.**

#### Note:

**Size 20** see No. 375370

### Technical description

Slot size b <sub>1</sub> of the machine	12 mm
Length	22 mm
Slot size b <sub>2</sub> of the jig	20 mm
for screws DIN 84, DIN 912	M6×10

Height H	10 mm
Type	6322A
Type of product	Tee-nut