




Stepped tenon ground, Slot size b1 of the machine: 14mm



Order data

Order number	375365 14
GTIN	4020772071578
Item class	35A

Description

Version:

Precision ground all round, resulting in quick alignment times for appliances, vices etc., which are to be aligned parallel to the table slots of machine tools. A dial indicator is thus no longer required.

Application:

These tenons are screwed in pairs into the standard 20mm-wide tenon slot of jigs. By changing the tenons it is possible to work **on several machines with different slot widths** with one jig each.

Material:

Steel C 15, case-hardened.

Accuracy:

Dimension b = fit h6.

Note:

Size 20 see No. 375370

Technical description

Slot size b ₂ of the jig	20 mm
Slot size b ₁ of the machine	14 mm
Length	25 mm
for screws DIN 84, DIN 912	M6×16

Height H	10 mm
Type	6322A
Type of product	Tee-nut