

**Try square Accuracy class 2, Stock length: 400X200mm****Order data**

| | |
|--------------|----------------|
| Order number | 452600 400X200 |
| GTIN | 4045197205827 |
| Item class | 42F |

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

| | |
|-----------------------|------------|
| Shank cross-section | 35×7 mm |
| Right angle tolerance | 0.06 mm |
| Stock length | 400×200 mm |
| Calibration | F1 |
| Standard | DIN 875 |
| Accuracy | 2 |

Type of product

Try squares

ServicesDAkkS calibration
Stock, try, and bevel edge squares
maximum arm length 750 mm

025010 750

Calibration
Stock, try, and bevel edge squares maximum
arm length 750 mm

025000 750