

Garant**Pull-down jaw, Jaw width: 80mm**

Order data

| | |
|--------------|---------------|
| Order number | 360084 80 |
| GTIN | 4045197481450 |
| Item class | 310 |

Description

Application:

Variable pitches can be achieved using crossed clamping rails.

Suitable for:

Clamping rail No. 360080.

Note:

For use with clamping rails from revision 3 onwards (see illustration). Attachment bar on multi-point clamping rails must not be wider than 5 mm.

Technical description

| | |
|----------------|---------|
| Clamping force | 5 kN |
| Clamping force | 10 kN |
| Clamping force | 15 kN |
| Clamping force | 20 kN |
| Torque | 6 Nm |
| Torque | 12 Nm |
| Torque | 17.5 Nm |

| | |
|-----------------------------|-----------|
| Torque | 25 Nm |
| Jaw width | 80 mm |
| max. stroke | 3 mm |
| T-bolt AF | 6 mm |
| Shank screw AF ₁ | 4 mm |
| Type of product | Vice jaws |