

**HOLEX**
**Protractor with adjustable beam, Graduated arc Ø×Stock length:  
100X150mm**

**Order data**

Order number	453400 100X150
GTIN	4045197205933
Item class	42F

**Description**
**Version:**

With longitudinally adjustable beam; beam end tapered 45°.

Open graduated arc with graduation 10 – 170°; reading 1°.

**Scale anti-glare satin chrome plated.** With clamping nut.

Calibration: F3

Scale divisions: 1 °

Error limit: ±30 '

**Technical description**

Stock length	150 mm
Graduated arc Ø	100 mm
Scale divisions	1 °
Error limit	±30 '
Standard	Manufacturer's standard
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Packaging	Wallet
Calibration	F3
Type of product	Protractor

**Services**

Labelling laser-etched Type	018940
Calibration Protractor	015360
DAkkS Calibration protractor GRAD	025820 GRAD
Calibration Protractor Type GRAD	025810 GRAD