



Protractor with adjustable beam, Graduated arc Ø×Stock length: 100X150mm



Order data

| | |
|--------------|----------------|
| Order number | 453400 100X150 |
| GTIN | 4045197205933 |
| Item class | 42F |

Description

Version:

With longitudinally adjustable beam; beam end tapered 45°.

Open semicircular graduated arc with graduation 10 – 170°; reading 1°.

Scale matt chrome-plated. With clamping nut.

Technical description

| | |
|------------------------|-------------------------|
| Stock length | 150 mm |
| Graduated arc Ø | 100 mm |
| Scale divisions | 1 degrees |
| Error limit | ±30 arc min. |
| Standard | Manufacturer's standard |
| Measurement technology | analogue |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | Wallet |
| Calibration | F3 |

Type of product

Protractor

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/453400-100X150>
