

**Collared washer Form G, for threads: M10****Order data**

Order number	375360 M10
GTIN	4020772081997
Item class	35A

**Description****Version:**

Form C and D case-hardened, form G quenched and tempered.

**Application:**

Due to its large diameter, form G is suitable even for clamping over the slot of forked clamps. Angular compensation up to 3° when used in sets.

**Standard:**

**DIN 6319** (Form G ähnlich DIN 6319).

**Technical description**

Bore $\varnothing d_2$	12 mm
Thickness $h_4$	5 mm
External $\varnothing d_5$	30 mm
for threads	M10
Type	6319G
Type of product	Collared washer

