

**Garant**
**ZeroClamp clamping pot, Type: 10148-SET**

**Order data**

Order number	360040 10148-SET
GTIN	4045197694713
Item class	310

**Description**
**Version:**

All components made of stainless or corrosion-resistant steel. The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

**Application:**

For individual incorporation in the clamping system.

**Supplied with:**

- Each with 4 clamping pots.
- 10 × adapters for the air line.
- 1.5 m air line.
- 1 × quick-release coupling No. 360019 size 10003.
- 1 × male coupling (suitable for quick-release coupling).

**Note:**

Supplied with drawings and installation instructions for configuring your own clamping system. 2-component epoxy resin may be used to fill in the milled slots.

**Technical description**

Indexing hole available	yes
Clamping pot Ø d	120 mm
Clamping pot No. 360040	10148
Series	ZeroClamp
Type of product	Clamping pot

---

## Accessories

Set of seals for clamping pot Ø 120 mm	360044 120
--	------------