



Collared washer Form G, for threads: M12



Order data

Order number	375360 M12
GTIN	4020772082000
Item class	35A

Description

Version:

Form C and D case-hardened, form G quenched and tempered.

Application:

Due to its large diameter, form G is suitable even for clamping over the slot of forked clamps. Angular compensation up to 3° when used in sets.

Standard:

DIN 6319 (Form G ähnlich DIN 6319).

Technical description

Thickness h_4	6 mm
External $\varnothing d_5$	36 mm
Bore $\varnothing d_2$	14.2 mm
for threads	M12
Type	6319G
Type of product	Collared washer

