

**Collared washer Form G, for threads: M14****Order data**

| | |
|--------------|---------------|
| Order number | 375360 M14 |
| GTIN | 4020772082017 |
| Item class | 35A |

Description**Version:**

Form C and D case-hardened, form G quenched and tempered.

Application:

Due to its large diameter, form G is suitable even for clamping over the slot of forked clamps. Angular compensation up to 3° when used in sets.

Standard:

DIN 6319 (Form G ähnlich DIN 6319).

Technical description

| | |
|----------------------------|-----------------|
| External $\varnothing d_5$ | 40 mm |
| Thickness h_4 | 6 mm |
| for threads | M14 |
| Bore $\varnothing d_2$ | 16.5 mm |
| Type | 6319G |
| Type of product | Collared washer |

