

**Stud DIN 6379, Thread M × length L: M20X315****Order data**

Order number	375380 M20X315
GTIN	4020772084998
Item class	35A

**Description****Version:**

Rolled thread.

**Application:**

For individual combination of T-bolts in conjunction with T-nuts and tenons No. 375315 – 375330, nuts No. 375385 – 378395 and plain washers No. 375340 – 375360.

**Standard:**

**DIN 6379**

**Material:**

Heat-treated steel

Strength class:

- **M6 – M12 = 10.9**
- **M14 – M30 = 8.8**

**Technical description**

Thread	M20×315
Length a	288 mm
Length b	200 mm
Type	6379
Type of product	Screw