



Protractor with adjustable beam, Graduated arc Ø×Stock length: 300X600mm



Order data

Order number	453400 300X600
GTIN	4045197205964
Item class	42F

Description

Version:

With longitudinally adjustable beam; beam end tapered 45°.

Open graduated arc with graduation 10 – 170°; reading 1°.

Scale anti-glare satin chrome plated. With clamping nut.

Calibration: F3

Scale divisions: 1 °

Error limit: ±30 '

Technical description

Graduated arc Ø	300 mm
Stock length	600 mm
Scale divisions	1 °
Error limit	±30 '
Standard	Manufacturer's standard
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Packaging	Wallet
Calibration	F3
Type of product	Protractor

Services

Labelling laser-etched Type	018940
Calibration Protractor	015360
Calibration Protractor Type GRAD	025810 GRAD
DAkkS Calibration protractor GRAD	025820 GRAD