

Garant**Pull-down jaw, Jaw width: 26mm**

Order data

Order number	360084 26
GTIN	4045197482082
Item class	310

Description

Application:

Variable pitches can be achieved using crossed clamping rails.

Suitable for:

Clamping rail No. 360080.

Note:

For use with clamping rails from revision 3 onwards (see illustration). Attachment bar on multi-point clamping rails must not be wider than 5 mm.

Technical description

Torque	6 Nm
Torque	12 Nm
Torque	17.5 Nm
Torque	25 Nm
Clamping force	5 kN
Clamping force	10 kN
Clamping force	15 kN
Clamping force	20 kN

Jaw width	26 mm
max. stroke	3 mm
T-bolt AF	6 mm
Shank screw AF ₁	4 mm
Type of product	Vice jaws