

**Try square Accuracy class 2, Stock length: 250X165mm****Order data**

Order number	452600 250X165
GTIN	4045197205803
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Shank cross-section	35×7 mm
Right angle tolerance	0.045 mm
Stock length	250×165 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Try squares

ServicesDAkkS calibration Stock, try, and bevel edge squares
maximum arm length 750 mm

025010 750

Calibration Stock, try, and bevel edge squares maximum
arm length 300 mm

025000 300

Accessories

Wooden case for stock length 250X165 mm

451600 250X165