



## Precision protractor, Beam length: 300mm



### Order data

Order number	453800 300
GTIN	4045197294623
Item class	46R

### Description

#### Version:

**Error-free reading.** The degree values are easily and clearly readable on a magnified 4×90° scale. The arc minutes are just as easily readable on a satin chrome-plated barrel with black scale markings. With double scale for both measurement directions. **Easy to handle quick adjustment and fine adjustment for the arc minute values. Satin chromium plated anti-glare reading parts.**

#### Supplied with:

1 stock square 60×90 mm for setting.

#### Optional extras:

Clamp No. 453520 (for fixing to scribers No. 445152 – 445222), attachment square No. 453600.

#### Spare part:

Measuring beam No. 453510. Magnifying glass No. 453820 size 2.

### Technical description

Beam length	300 mm
Scale divisions	1 arc min.
Spindle pitch	1 degrees
Error limit	±2 arc min.
Measuring range	360 degrees
Standard	Manufacturer's standard
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Packaging	sturdy box
Calibration	F4
Type of product	Protractor

### Services

CalibrationUniversal protractor Type UNI	025710 UNI
--	------------

### Accessories

Attachment square	453600
Spare magnifying glass for protractor Type 2	453820 2
Holder for clamping the protractor	453520
Spare blade, slot width 2.5 mm Beam length 300 mm	453510 300