



## Micrometer head, Measuring range (travel): 0-25mm



### Order data

Order number	426250 0-25
GTIN	4045197204097
Item class	42B

### Description

#### Version:

Fully hardened spindle and glare-free satin chrome-plated barrel. **Rotating spindle**, with carbide tipped contact face and ratchet.

#### Application:

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.

### Technical description

Length of mounting shank	17 mm
Measuring range (travel)	0 - 25 mm
Overall length	113 mm
Spindle Ø	6.5 mm
Mounting shank Ø	12 mm
Barrel Ø	18 mm
Scale divisions	0.01 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B3

Type of product	Micrometer head
-----------------	-----------------

## Services

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
--	-----------

DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50
--	-----------