

**Mitutoyo****Internal micrometer, Measuring range: 50-75mm****Order data**

Order number	426805 50-75
GTIN	4946368019895
Item class	44A

**Description****Version:**

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

**Optional extras:**

Setting ring No. 484030.

**Technical description**

Barrel Ø	18 mm
Measuring range	50 - 75 mm
Scale divisions	0.01 mm
Error limit	7 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

**Services**

CalibrationInternal micrometer maximum measuring range 75 mm

022360 75

## Accessories

Setting ringDIN 2250 C Nominal size Ø 75 mm

484030 75

Setting ringDIN 2250 C Nominal size Ø 70 mm

484030 70

Setting ringDIN 2250 C Nominal size Ø 50 mm

484030 50

Setting ringDIN 2250 C Nominal size Ø 65 mm

484030 65

Setting ringDIN 2250 C Nominal size Ø 55 mm

484030 55

Setting ringDIN 2250 C Nominal size Ø 60 mm

484030 60