



Depth micrometer, Measuring range: 0-100mm



Order data

Order number	425300 0-100
GTIN	4045197578907
Item class	42B

Description

Version:

Various measuring depths can be achieved by exchanging the measuring pins with 25 mm increments. Measuring spindle fully hardened and ground. Base of hardened tool steel with lapped measuring anvil. Micrometer satin chrome-plated. Barrel with clearly engraved black scale and numerals. Constant measuring force due to integral ratchet.

Supplied with:

Measuring pins.

Technical description

Number of gauging pins	4
Measuring needle \varnothing	4.5 mm
Bridge length	100 mm
Barrel \varnothing	18 mm
Measuring range	0 - 100 mm
Scale divisions	0.01 mm
Standard	DIN 863

Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S15
Type of product	Depth micrometer

Services

CalibrationDepth micrometer set Measuring range 0-100 mm	020780 0-100
--	--------------