



Internal micrometer, Measuring range: 30-40mm



Order data

Order number	427800 30-40
GTIN	2050001038067
Item class	43A

Description

Version:

Lightweight, kink-proof tubular construction. Measuring spindle through hardened and ground. **Measuring faces hardened and spherical lapped.** Control elements and reading parts satin chrome-plated. From measuring range 100 - 125 mm with thermal insulation and locking lever.

Supplied with:

Micrometer in a sleeve.

Technical description

Barrel Ø	12.5 mm
Spindle Ø	7 mm
Measuring range	30 - 40 mm
Scale divisions	0.01 mm
Error limit	4 µm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B10
Type of product	2-point internal micrometer

Services

Calibration Internal micrometer maximum measuring range 100 mm

022440 100

DAkkS calibration Internal micrometer maximum measuring range 200 mm

022450 200