



Micrometer head, Measuring range (travel): 0-25/Fmm



Order data

Order number	426250 0-25/F
GTIN	4045197204103
Item class	42B

Description

Version:

Fully hardened spindle and glare-free satin chrome-plated barrel. **Stationary (non-rotating)** spindle with carbide tipped contact face and ratchet. For checking materials with delicate surfaces.

Application:

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.

Technical description

Barrel Ø	18 mm
Length of mounting shank	10 mm
Spindle Ø	8 mm
Overall length	113 mm
Mounting shank Ø	12 mm
Scale divisions	0.002 mm
Error limit	0.003 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Calibration	B3
Type of product	Micrometer head

Services

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50