



Depth micrometer, Measuring range: 0-150mm



Order data

Order number	425300 0-150
GTIN	4045197578914
Item class	42B

Description

Version:

Various measuring depths can be achieved by exchanging the measuring pins with 25 mm increments. Measuring spindle fully hardened and ground. Base of hardened tool steel with lapped measuring anvil. Micrometer satin chrome-plated. Barrel with clearly engraved black scale and numerals. Constant measuring force due to integral ratchet.

Supplied with:

Measuring pins.

Technical description

Measuring range	0 - 150 mm
Bridge length	100 mm
Barrel Ø	18 mm
Number of gauging pins	6
Measuring needle Ø	4.5 mm
Scale divisions	0.01 mm
Standard	DIN 863

Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S15
Type of product	Depth micrometer

Services

CalibrationDepth micrometer set Measuring range 0-150 mm	020780 0-150
--	--------------