

 Mahr**Micrometer with dial comparator, Measuring range: 0-25mm****Order data**

Order number	422500 0-25
GTIN	4059192004248
Item class	43A

**Description****Version:**

Measuring spindle through hardened and ground.

With precision lapped **carbide tipped anvils**.

Spindle and anvil of stainless steel.

One piece frame and spindle guide.

Button for retracting the measurement anvil for repetitive measurements.

With adjustment screw for zeroing.

Tolerance pointers for good/ reject measurements.

With hand temperature protection. Lever for spindle clamping.

**Callout:**

Deviation read-off in 1/1000 mm.

Push button for anvil retraction.

**Accuracy:**

**Dial comparator 1  $\mu\text{m}$  – micrometer 2  $\mu\text{m}$ .**

**Technical description**

Measuring range dial comparator	$\pm 0.065$ mm
Measuring range	0 - 25 mm
Clearance depth of micrometer frame	16 mm

Graduation of the precision dial comparator	0.001 mm
Graduation of the micrometer	0.01 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B9
Type of product	Micrometer with dial comparator

## Services

CalibrationIndicator micrometer maximum measuring range 25 mm	022100 25
---	-----------