

Mitutoyo**Internal micrometer, Measuring range: 75-100mm****Order data**

Order number	426805 75-100
GTIN	4946368019901
Item class	44A

Description**Version:**

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

Optional extras:

Setting ring No. 484030.

Technical description

Barrel Ø	18 mm
Measuring range	75 - 100 mm
Scale divisions	0.01 mm
Error limit	8 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

Services

CalibrationInternal micrometer maximum measuring range 100 mm

022360 100

Accessories

Setting ringDIN 2250 C Nominal size Ø 125 mm

484030 125

Setting ringDIN 2250 C Nominal size Ø 275 mm

484030 275

Setting ringDIN 2250 C Nominal size Ø 85 mm

484030 85

Setting ringDIN 2250 C Nominal size Ø 175 mm

484030 175

Setting ringDIN 2250 C Nominal size Ø 225 mm

484030 225

Setting ringDIN 2250 C Nominal size Ø 80 mm

484030 80

Setting ringDIN 2250 C Nominal size Ø 95 mm

484030 95

Setting ringDIN 2250 C Nominal size Ø 100 mm

484030 100

Setting ringDIN 2250 C Nominal size Ø 75 mm

484030 75

Setting ringDIN 2250 C Nominal size Ø 90 mm

484030 90