



## Internal micrometer, Measuring range: 40-50mm



### Order data

Order number	427800 40-50
GTIN	2050001053626
Item class	43A

### Description

#### Version:

**Lightweight, kink-proof tubular construction.** Measuring spindle through hardened and ground. **Measuring faces hardened and spherical lapped.** Control elements and reading parts satin chrome-plated. From measuring range 100 - 125 mm with thermal insulation and locking lever.

#### Supplied with:

Micrometer in a sleeve.

### Technical description

Measuring range	40 - 50 mm
Barrel Ø	12.5 mm
Spindle Ø	7 mm
Scale divisions	0.01 mm
Error limit	4 µm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B10
Type of product	2-point internal micrometer

---

**Services**

Calibration Internal micrometer maximum measuring range 100 mm

022440 100

DAkkS calibration Internal micrometer maximum measuring range 200 mm

022450 200