

Mitutoyo
Digital micrometer head with data output, Measuring range (travel): 0-25mm


Order data

Order number	426510 0-25
GTIN	4946368695976
Item class	44A

Description

Version:

Direct reading from clear digital display. Reliable and error-free measurements - without a vernier. Hardened and ground measuring spindle, locking by clamping screw, ratchet.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable micrometer stop.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445.

Technical description

Barrel Ø	18 mm
Length of mounting shank	16 mm
Spindle Ø	6.35 mm
Measuring range (travel)	0 - 25 mm
IP Index of Protection	IP 65
Overall length	170 mm

Mounting shank Ø	12 mm
Scale divisions	0.001 mm
Error limit	0.002 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Calibration	B3
Type of product	Micrometer head

Services

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50

Accessories

Connecting cablewith data switch Type D2	497445 D2
Receiver / USB keyboard interface Type	498965
Transmitter Type S16E	498966 S16E
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Connecting cablewith data switch Type D1	497445 D1
Connecting cablewith data switch Type USB2	497445 USB2