

Mitutoyo**Digital depth micrometer with data output, Measuring range: 0-150mm****Order data**

Order number	425400 0-150
GTIN	4946368695846
Item class	44A

Description**Version:**

Clear (7.5 mm high), digital measured value display provides quick, error-free readings. Addition reading by vernier.

Various measuring depths can be achieved by exchanging the measuring pins with 25 mm increments. Measuring spindle fully hardened and ground. Base of hardened tool steel with lapped measuring anvil. Micrometer satin chrome-plated. Barrel with clearly engraved black scale and numerals. Constant measuring force due to integral ratchet.

Callout:**Data storage button:**

The measurement result can be stored by pressing a button. (E.g. If the measurement position is awkward).

Zero point / absolute size:

Enables zeroing at any position. Absolute zeroing is restored by pressing the button again.

Preset button:

For "zeroing". This setting is retained after switching off the display.

Supplied with:

Measuring pins and 1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445.

Technical description

Number of gauging pins	6
Bridge length	100 mm
Measuring range	0 - 150 mm
Measuring needle Ø	4 mm
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S15
Type of product	Depth micrometer

Services

CalibrationDepth micrometer set Measuring range 0-150 mm	020780 0-150
--	--------------

Accessories

Transmitter Type S16E	498966 S16E
Connecting cablewith data switch Type USB2	497445 USB2
Connecting cablewith data switch Type D1	497445 D1
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Receiver / USB keyboard interface Type	498965

Connecting cable with data switch Type D2

497445 D2